

Legacy Speakers

Rocket 50 (Legacy)

12-inch steel-chassis guitar speaker



Look inside the back of a standard 4x12 and you may well find a quartet of Rocket 50s. This speaker performs well with any playing style, and won't break the bank.

General Specifications

Nominal Diameter	305mm / 12in
Power Rating	50W
Rated impedance	8 Ω or 16 Ω
Sensitivity	95dB
Chassis type	Pressed steel
Magnet type	Ceramic
Magnet weight	0.48kg / 17oz
Voice coil diameter	38mm / 1.5in
Voice coil material	Round copper
Frequency range	85-5000Hz
Resonance frequency Fs	90Hz
DC resistance, Re	6.74 & 12.44

Mounting Information

Cut-out diameter	283mm / 11.1in
Diameter	309mm / 12.2in
Magnet structure diameter	100mm / 3.9in
Mounting hole dimensions	7.9mm / 0.31in
Mounting hole PCD	297mm / 11.7in
Number of mounting holes	4
Chassis depth (inc gasket)	95mm / 3.72in
Magnet depth	27mm / 1.08in
Overall depth	122mm / 4.8in
Unit weight	2.0kg / 4.4lb

8 Frequency Response

