



Part Number : 987891208

Series Number : 98789

Product Category : Connector Housings

Product Description : NSCC Single Part, Non-Sealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Gray


Status : New Business Not Supported

Engineering Number : 09218EV10F8

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Connector Housings

Series	98789
Description	NSCC Single Part, Non-Sealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Gray
Application	Power, Wire-to-Wire
Product Family	NSCC - New Standard Casing Contact
Product Name	NSCC
UPC	822350007146

Physical

Circuits Detail	10
Circuits (maximum)	10
Color - Resin	Gray
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	11.470/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.25mm
Pitch - Termination Interface	6.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +120°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Extractor Tool for CTX64 Female Crimp Terminals	<u>638135700</u>

This document was generated on Jul 22, 2024