

Han® ORV3 LMC-F-CRT-6mm²/AWG10-Ag



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 000 6243
Specification	Han® ORV3 LMC-F-CRT-6mm ² /AWG10-Ag
HARTING eCatalogue	https://b2b.harting.com/09930006243

Identification

Category	Contacts
Series	Han® ORV3 power
Type of contact	Crimp contact

Version

Gender	Female
Manufacturing process	Turned contacts
Details	Contacts for the use in combination with the ORV3 connector.

Technical characteristics

Conductor cross-section	6 mm ²
Conductor cross-section [AWG]	AWG 10
Rated current	≤32 A
Contact resistance	≤0.6 mΩ
Stripping length	11 mm
Mating cycles	≥100

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated



Pushing Performance
Since 1945

Specifications and approvals

Specifications	OCP V1.0
----------------	----------

Commercial data

Packaging size	25
Net weight	1 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140463264
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors