

# CT3810

## Alligator Clip Test Lead

# Datasheet

Pair, black & red, insulated alligator clip to insulated alligator...

### Description

Black and red pair of standard insulated alligator clip to standard insulated alligator clip test leads. Alligator clips have insulated PVC boots. Test lead wire is 18 AWG with highly flexible silicone jackets.

Features:

- Materials:
- Body & spring: steel, nickel plated
- Insulator: PVC
- Wire: high stranded bare copper; silicone jacket
  
- Jaws open to 7.9 mm (0.31")
- Black & red pair
- Available in 3 lengths
- IEC 61010-031 rated

Available as individual colors Model CT3809



*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

**Cal Test**  
ELECTRONICS 

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

### Specifications

<b>Voltage Rating</b>	300 V CAT II
<b>Current, Max</b>	10 A
<b>Jacket Material</b>	Silicone
<b>Wire Gauge</b>	18 AWG (0.82 mm <sup>2</sup> )
<b>Stranding (# x dia.)</b>	168 x 0.07 mm
<b>Jacket OD</b>	3.7 mm (0.146")
<b>Temperature (degrees)</b>	-20 to +80C
<b>RoHS (2011/65/EU)</b>	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

