

CT3230

BNC male to IC Test Clip

High Quality BNC to IC test clip breakout cable Molded...

Description

High Quality BNC male cable assembly to IC test clip breakout.

Molded bend relief boot.

- Materials: Body: Brass or Zinc, Nickel Plt.; Contact: Brass, Gold Plt.; Boot: PVC, Black
- IC Clip Contact: BeCu, Gold Plt.



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

Voltage Max.	500 Vrms
Current Max.	3 A
Impedance, ohm	50 Ohm
Cable Type	RG-58C/U
Jacket Material	PVC
Temperature (degrees)	0 to +50 degC
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

