

CT3760

Insulated Alligator Clip

Datasheet

Pair, black & red, standard alligator clips with PVC insulators,...

Description

Black and red pair of standard alligator clips with flexible PVC insulators. The clips accept 2 mm pin tips. Example is 2 mm (.080") diameter probe tips.

Features:

- Materials:
 - Body & spring: steel, nickel plated
 - Insulator: PVC
 - Pin tip contact: Phosphor bronze, gold plated
- Pair, black and red
- Overall length: 56 mm (2.21")
- Jaws open to 7.9 mm (0.31")
- IEC 61010-031 rated

Individual color alligator clips available as Model 3759



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

Voltage	300 V CAT II
Current Max.	10 A
Temperature (degrees)	0 to +60C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

