

# CT3388

## Coaxial Adapter In-Series

N Right-Angle, male to female, General Purpose

### Description

N Type right-angle, male to female, 50 in-series coaxial adapter.



*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

# Datasheet

**Cal Test**  
ELECTRONICS 

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

### Specifications

<b>Connector Grade</b>	General Purpose
<b>Impedance, ohm</b>	50
<b>Frequency Range</b>	DC to 8 GHz (various)
<b>VSWR Max</b>	1.35:1 - DC to 8 GHz
<b>Insertion Loss Max</b>	-
<b>Temperature (degrees)</b>	-20 to +80C
<b>RoHS (2011/65/EU)</b>	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

