

PW 504409 T



Sample image

Order symbol : PW 504409 T

Product nr : 4901844

Description : PW Inspection Protection window,

Remarks : 503x451x88 mm, DB3 lock, Transparent cover

EAN : 6418074320483

El. number :

- Finland : 3424739
- Sweden : 2507625

4901844_FIBOX_PW_504409_T DIM

Dimensions :	Height	Width	Depth
mm :	503	451	88
inch :	19.8	17.76	3.46

Materials :

Material :	Polycarbonate
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK09;
electrical_insulation :	Not insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C
UL Type	4, 4X, 12 and 13