


BU-4150081XXX

(Cable Assembly Coaxial SMA Straight to SMA Straight Male to Male RG-086, Hand-Formable)



Electrical Ratings

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

Connector	Cable	Connector	Frequency	VSWR	Working	
		Impedance	(GHz)		Voltage	
		(Ohms)			(At Sea	
					Level)	
SMA	RG-086	50	DC-18	1.3 MAX	335V	

Product Attributes

Gender	Male to Male		
Style	SMA to SMA		
1st Connector	Gold Plated SMA Male Plug Straight		
2nd Connector	Gold Plated SMA Male Plug Straight		
Features	Shielded		
Operating Temperature	-65°C (-85°F) to 150°C (302°F)		
BU-4150081003	3" (76.2 mm)		
BU-4150081004	4" (101.6 mm)		
BU-4150081005	5" (127 mm)		
BU-4150081006	6" (152.4 mm)		
BU-4150081007	7" (177.8 mm)		
BU-4150081008	8" (203.2 mm)		
BU-4150081012	12" (304.8 mm)		
BU-4150081018	18" (457.2 mm)		
BU-4150081024	24" (609.6 mm)		
BU-4150081MM150	150mm (5.9")		
BU-4150081MM750	750mm (29.5")		
RoHS 3 Compliant			

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524