


## BU-4150088XXX

(Cable Assembly Coaxial U.FL Female to U.FL Female 1.37mm Ø Cable)





Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

## **Electrical Ratings**

Electrical ratings of a cable assembly are determined by the limiting connector type and cable size.

Connector	Cable	Connector Impedance (Ohms)	Frequency (GHz)	VSWR	Working Voltage (At Sea Level)
U.FL	Ø1.37mm	50	DC-1	1.3 MAX	335V

## **Product Attributes**

Gender	Female to Female		
Style	U.FL to U.FL		
1st Connector	Gold Plated U.FL Female Plug		
2nd Connector	Gold Plated U.FL Female Plug		
Features	Shielded		
Operating Temperature	-65°C (-85°F) to 150°C (302°F)		
BU-4150088050	50 mm (2")		
BU-4150088100	100 mm (3.9")		
BU-4150088150	150 mm (5.9")		
BU-4150088200	200 mm (7.9")		
BU-4150088250	250mm (9.8")		
BU-4150088300	300 mm (11.8")		
BU-4150088500	500mm (19.7")		
RoHS 3 Compliant			

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524