



GME423TAA

3-Button Optical USB Wired Mouse

The TAA- Compliant IOGEAR 3-Button Optical Wired Mouse offers smooth, precise cursor movement for your everyday computing needs. Equipped with left, right and center buttons, a scroll-wheel, and an optical tracking 1000 DPI sensor, the 3-Button Optical Wired Mouse is ready to be connected to your preferred docking station, desktop or KVM.



Features

- High-sensitivity optical sensor
- Delivers smooth, precise cursor movement
- Left, right and scroll button/wheel
- 6ft cable
- USB 2.0 connector
- 1000 Dpi sensor

Requirements

- Windows® 10, Windows® 11
- Mac OS X 10.3+
- USB-A Port

Package Contents

- 1x GME423



Specifications

FUNCTION	GME423TAA	DIMENSIONS	GME423TAA
Housing		Unit Dimensions	
Case	ABS Plastic	Height	1 in (2.54 cm)
Operating System Support	Windows 7,10, 11 and Mac OS 10.7+	Length	4.4" (11.17 cm)
Connectors		Width	2.4 in (6 cm)
Cable	USB-A (6ft)	Inner Pack	
Mouse	3-button mouse	Height	9 in (23 cm)
		Length	7.6 in (19.5 cm)
		Width	6 in (15.4 cm)
		Inner Pack Qty.	12 pcs
		Unit Package Dimensions	
		Height	1.4 in (3.6 cm)
		Length	5.3 in (13.4 cm)
		Width	3.6 in (9.2 cm)
		Master Carton	
		Height	18.9 in (48 cm)
		Length	15.9 in (40.5 cm)
		Width	7 in (18 cm)
		Master Carton Qty.	48 pcs
		Weight	
		Master Carton Wt.	14.6 lb (6.65 kg)
		Inner Pack Wt.	3.17 lbs (1.44 kg)
		Unit Pack Wt.	0.25 lbs (0.10 kg)
		Unit Wt.	0.20 lbs (0.08 kg)