



GWKIT4K

# 4K HDMI® Wireless Video TV Connection Kit

The IOGEAR 4K HDMI® Wireless Video TV Connection Kit is a device that allows you to wirelessly stream 4K video and audio from your 4K game consoles, Blu-Ray® players, set top boxes or from your Windows 10/11 PC, MacOS X, to your 4K UHD TV, projector or monitor.



HDMI®  
HIGH DEFINITION MULTIMEDIA INTERFACE



## Features

---

- Wirelessly mirror your HDMI source such as a Blu-Ray™ player or laptop with an HDMI™ output to a 4K display screen or 4K projector
- Maximum resolutions of 4K @30Hz
- Wireless 2.4/5 GHz using WPA-2 encryption with 128-bit AES
- Range up to 100 ft under optimal conditions
- Transmitting from your device to a big monitor takes less than a minute
- Comes pre-paired making setup a simple task by connecting HDMI cables and powering the transmitter and the receiver on
- Supports most video sources with HDMI input/output port
- Can go through some obstructions

## Requirements

---

### Plug and Play Mode

- Source with HDMI output.
- Display with HDMI input.

## Package Contents

---

- 1 x Transmitter
- 1 x Receiver
- 1 x Power Adapter for Receiver
- 1 x USB to USB Micro Power Cable for Transmitter
- 2 x HDMI Cables
- 1 x Quick Start Guide
- 1 x Warranty Card



## Specifications

FUNCTION	GWKIT4K	DIMENSIONS	GWKIT4K
Housing		POP Information	
Case	Plastic	10" Peg Hook	3
Video connections		Unit Dimensions	
Input	HDMI	Height	TX 3.125" RX 3"
Output	HDMI	Width	TX 5.625" RX 3.25"
Frequency Band	802.11 ac/5 GHz	Depth	TX 1" RX 0.625"
Video Resolution	4K @30Hz	Inner Pack	
Audio		Height	9.825"
Audio Output	2-Channel 16-bit AAC	Width	12.50"
Sample Rate	48 kHz 16-bit from HDMI connector	Depth	9.75"
Antenna Type	tx: built-in rx: Single SMA	Inner Pack Qty.	6
Operating Range	100 ft.	Unit Package Dimensions	
Operating Temperature	32~104°F (0~40°C)	Height	5.75"
Environment		Width	9.25"
Storage Temperature	14~158°F (-10~70°C)	Depth	3"
Humidity	10% to 85% RH (Non condensing)	Master Carton	
Power		Height	11.75"
Voltage	tx: 5V/1A rx: 5V/0.50A	Width	21.25"
		Depth	13.50"
		Master Carton Qty.	12
		Weight	
		Master Carton Wt.	23.20 lb
		Inner Pack Wt.	10.55 lb
		Unit Pack Wt.	1.60 lb
		Unit Wt.	TX 0.10 lb RX 0.25 lb