



GCS92HU

2-Port 4K KVM Switch with HDMI, USB and Audio Connections

One of the most compact KVMs IOGEAR has to offer, the 2-Port 4K KVM Switch with HDMI Connection, USB and Audio is a must-have for users with two computers using one monitor, keyboard and mouse. It is perfect for a home office or small to medium-sized business that need to conserve workspace and streamline desktop setups.



HDMI[®]
HIGH DEFINITION MULTIMEDIA INTERFACE



Features

- One USB keyboard, mouse and one HDMI monitor control two HDMI computers
- Superior video quality – up to 4K DCI (4096 x 2160 @ 60Hz)
- Computer selection via remote port selector
- HDMI compliant; [HDCP 2.2](#) compliant
- Supports USB hot-plugging
- The console USB ports can be used for USB peripheral sharing
- Multiplatform support – Windows, Mac and Linux
- Plug and play
- Bus-powered – no external power adapter required¹

Note: 1. The GCS92HU may require an external power supply via the USB Micro-B Power Port. For the USB Micro-B cable connecting to the USB Micro-B Power Port, it requires a separate purchase based on the type of the power supply you use.

Requirements

Console

- HDMI monitor
- Standard 104-key wired USB keyboard
- Standard 2 or 3 button wired USB mouse
- Speakers and Microphones (optional)

Computers

- HDMI port
- USB Type-A port
- Audio ports (optional)

Operating Systems

Package Contents

- 1x GCS92HU 2-Port 4K KVM Switch with HDMI Connection, USB and Audio
- 1x Quick Start Guide
- 1x Warranty Card

www.iogear.com



- Windows®7, 8.1, 10, 11
- Mac OS X 9.0+
- Oracle® Solaris
- Linux®, UNIX, and other USB supported systems



Specifications

FUNCTION	GCS92HU	DIMENSIONS	GCS92HU
Computer Connections		Unit Dimensions	
Direct	2	Height	1.06" (2.69cm)
Port Selection	Remote Pushbutton	Length	3.375" (8.57cm)
Console Connectors		Depth	3.25" (8.27cm)
Monitor	1x HDMI	Unit Package Dimensions	
Keyboard	1 x USB Type A	Height	8.875" (22.5cm)
Mouse	1 x USB Type A	Length	6.125" (15.56cm)
Audio	1 x 3.5mm Mini Stereo Jack (Green)	Depth	2.18" (5.54cm)
Microphone	1 x 3.5mm Mini Stereo Jack (Pink)	Master Carton	
CPU Connectors		Height	6.75" (17.15cm)
Monitor	2 x HDMI	Length	15.25" (38.74cm)
Keyboard & Mouse	2 x USB 2.0 Type A	Depth	8" (20.3cm)
Audio	2 x 3.5mm Mini Stereo Jack(Green)	Master Carton Qty.	6
Microphone	2 x 3.5mm Mini Stereo Jack(Pink)	Weight	
LEDs		Master Carton Wt.	7.0 lb. (3.18kg)
KVM	2 x White	Unit Pack Wt.	1.05 lb (0.48 kg)
Video Resolution	up to 4096 x 2160 @60Hz	Unit Wt.	0.8 lb (0.36 kg)
Cable Length	KVM cables: 48" (121.92cm)		
Environment			
Operation Temperature	0~50C (32~122 F)		
Storage Temperature	-20~60C (-4~140F)		
Humidity	0~80% RH, Non-condensing		
Housing			
Case	Plastic		