



GCS32HU

2-Port HDMI KVM Switch with HDMI and USB Connections

IOGEAR's 2-Port HDMI KVM switch with HDMI and USB connections enables effortless control over 2 HDMI full HD computers using a single USB keyboard, a USB mouse and an HDMI monitor.



HDMI
HIGH DEFINITION MULTIMEDIA INTERFACE



Features

- One USB keyboard, USB mouse, and HDMI monitor controls two HDMI computers
- Full HD video quality - up to 1920x1200@60Hz
- Plug-n-Play monitor support
- Molded-in cables to simplify setup
- Compact design features two attached KVM (USB and HDMI) cables
- Supports Windows® 7, 8.1, 10, 11, Mac OS® X 9.0+, Linux®, Unix and other USB supported systems
- No software drivers required – simply connect the cables to the computers
- Computer selection via 6 ft remote controller cable that can be placed on your desk for easy reach
- Mac keyboard support
- No power adapter required

Requirements

Console:

- 1 HDMI display
- Standard 104 key wired USB keyboard
- Standard 2 or 3 button wired USB mouse

Computers:

- 1 HDMI port
- 2 USB ports

Operating Systems:

- Windows® 7, 8.1, 10, 11
- Mac OS® X 9.0+
- Linux®, Unix and other USB supported systems*

Package Contents

- 1 x GCS32HU 2-Port Full HD KVM Switch with HDMI and USB Connections
- 1 x Quick Start Guide
- 1 x Warranty Card

www.iogear.com



*Additional drivers and support may be needed



Specifications

FUNCTION	GCS32HU	DIMENSIONS	GCS32HU
Computer Connections		Unit Package Dimensions	
Direct	2	Height	8.75 in.
Port Selection	Remote Pushbutton	Length	6.13 in.
Console Connectors		Width	2.25 in.
Monitor	1 x HDMI	Master Carton	
Keyboard	1 x USB Type A	Height	7 in.
Mouse	1 x USB Type A	Length	8 in.
CPU Connectors		Width	15.25 in.
Monitor	2 x HDMI	Master Carton Qty.	6
Keyboard & Mouse	2 x USB 2.0 Type A	Weight	
LEDs		Master Carton Wt.	5.75 lbs.
KVM	2 x White	Unit Pack Wt.	0.85 lb.
Cable Length	4 ft.		
Video Resolution	up to 1920 x 1200 @60Hz		
Environment			
Operation Temperature	0~50C (32~122 F)		
Storage Temperature	-20~60C (-4~140F)		
Humidity	0~80% RH, Non-condensing		
Housing			
Case	Plastic		