

## M17 Crimp Contact 0,6mm, FE,0,08-0,14mm<sup>2</sup>



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 062 0000
Specification	M17 Crimp Contact 0,6mm, FE,0,08-0,14mm <sup>2</sup>
HARTING eCatalogue	<a href="https://b2b.harting.com/21170620000">https://b2b.harting.com/21170620000</a>

### Identification

Category	Contacts
Series	Circular connectors M17
Type of contact	Crimp contact

### Version

Gender	Female
Manufacturing process	Turned contacts

### Technical characteristics

Conductor cross-section	0.08 ... 0.14 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 28 ... AWG 26
Stripping length	5 mm
Limiting temperature	-40 ... +125 °C

### Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
-----------------------	---------------

---

## Commercial data

Packaging size	100
Net weight	0.16 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140819825
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors