

M17 Crimp Contact 1,5mm,male,0,75-1,0mm²



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 075 0000
Specification	M17 Crimp Contact 1,5mm,male,0,75-1,0mm ²
HARTING eCatalogue	https://b2b.harting.com/21170750000

Identification

Category	Contacts
Series	Circular connectors M17
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section [AWG]	AWG 19 ... AWG 17
Stripping length	7 mm
Limiting temperature	-40 ... +125 °C

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

