

Surface-mount Ceramic Multilayer Capacitors (RoHS compliant & Halogen Free)

CC1206000000SB000

CC1206 Commodity Sample Kit

Spec Sheet

Scope

This product specification is applied to Multi-layer Ceramic Capacitor used for General Electronic equipments .



No.	Part NO.	Size	TC	Cap.	Volt.	Tol	No.	Part NO.	Size	TC	Cap.	Volt.	Tol
1	CC1206CRNPO9BN2R7	1206	NPO	2.7pF	50V	±0.25pF	26	CC1206KRX7R8BB224	1206	X7R	220nF	25V	±10%
2	CC1206JRNPO9BN100	1206	NPO	10pF	50V	±5%	27	CC1206KKX7R8BB334	1206	X7R	330nF	25V	±10%
3	CC1206JRNPO9BN150	1206	NPO	15pF	50V	±5%	28	CC1206KRX7R8BB474	1206	X7R	470nF	25V	±10%
4	CC1206JRNPO9BN220	1206	NPO	22pF	50V	±5%	29	CC1206KKX7R8BB684	1206	X7R	680nF	25V	±10%
5	CC1206JRNPO9BN330	1206	NPO	33pF	50V	±5%	30	CC1206KRX7R9BB221	1206	X7R	220pF	50V	±10%
6	CC1206JRNPO9BN470	1206	NPO	47pF	50V	±5%	31	CC1206KRX7R9BB331	1206	X7R	330pF	50V	±10%
7	CC1206JRNPO9BN101	1206	NPO	100pF	50V	±5%	32	CC1206KRX7R9BB471	1206	X7R	470pF	50V	±10%
8	CC1206JRNPO9BN151	1206	NPO	150pF	50V	±5%	33	CC1206KRX7R9BB102	1206	X7R	1nF	50V	±10%
9	CC1206JRNPO9BN221	1206	NPO	220pF	50V	±5%	34	CC1206KRX7R9BB222	1206	X7R	2.2nF	50V	±10%
10	CC1206JRNPO9BN331	1206	NPO	330pF	50V	±5%	35	CC1206KRX7R9BB332	1206	X7R	3.3nF	50V	±10%
11	CC1206JRNPO9BN471	1206	NPO	470pF	50V	±5%	36	CC1206KRX7R9BB472	1206	X7R	4.7nF	50V	±10%
12	CC1206JRNPO9BN681	1206	NPO	680pF	50V	±5%	37	CC1206KRX7R9BB682	1206	X7R	6.8nF	50V	±10%
13	CC1206JRNPO9BN102	1206	NPO	1nF	50V	±5%	38	CC1206KRX7R9BB103	1206	X7R	10nF	50V	±10%
14	CC1206JRNPO9BN182	1206	NPO	1.8nF	50V	±5%	39	CC1206KRX7R9BB153	1206	X7R	15nF	50V	±10%
15	CC1206JRNPO9BN222	1206	NPO	2.2nF	50V	±5%	40	CC1206KRX7R9BB223	1206	X7R	22nF	50V	±10%
16	CC1206JRNPO9BN272	1206	NPO	2.7nF	50V	±5%	41	CC1206KRX7R9BB333	1206	X7R	33nF	50V	±10%
17	CC1206JRNPO9BN332	1206	NPO	3.3nF	50V	±5%	42	CC1206KRX7R9BB473	1206	X7R	47nF	50V	±10%
18	CC1206JRNPO9BN472	1206	NPO	4.7nF	50V	±5%	43	CC1206KRX7R9BB563	1206	X7R	56nF	50V	±10%
19	CC1206JKNPO9BN103	1206	NPO	10nF	50V	±5%	44	CC1206KRX7R9BB683	1206	X7R	68nF	50V	±10%
20	CC1206JRNPO9BN333	1206	NPO	33nF	50V	±5%	45	CC1206KRX7R9BB104	1206	X7R	100nF	50V	±10%
21	CC1206KRX7R7BB224	1206	X7R	220nF	16V	±10%	46	CC1206KKX7R9BB154	1206	X7R	150nF	50V	±10%
22	CC1206KRX7R7BB394	1206	X7R	390nF	16V	±10%	47	CC1206KKX7R9BB224	1206	X7R	220nF	50V	±10%
23	CC1206KRX7R7BB474	1206	X7R	470nF	16V	±10%	48	CC1206KRX7R9BB334	1206	X7R	330nF	50V	±10%
24	CC1206KKX7R7BB684	1206	X7R	680nF	16V	±10%	49	CC1206KKX7R9BB474	1206	X7R	470nF	50V	±10%
25	CC1206KRX7R8BB104	1206	X7R	100nF	25V	±10%	50	CC1206KKX7R9BB684	1206	X7R	680nF	50V	±10%

Piecs per items: Case size 01005 to 0402, 80pcs; 0603 to 1808, 40pcs; 1812, 20pcs.