

**Surface-mount Ceramic Multilayer Capacitors (RoHS compliant & Halogen Free)**

CQ0402000000SB000

Hi-Frequency 0402 Sample Kit

Spec Sheet

**Scope**

This product specification is applied to Multi-layer Ceramic Capacitor used for High Frequency application .



No.	Part NO.	Size	TC	Cap.	Volt.	Tol	No.	Part NO.	Size	TC	Cap.	Volt.	Tol
1	CQ0402BRNPO9BNR20	0402	NPO	0.2pF	50 V	±0.1pF	23	CQ0402BRNPO9BN3R9	0402	NPO	3.9pF	50 V	±0.1pF
2	CQ0402BRNPO9BNR30	0402	NPO	0.3pF	50 V	±0.1pF	24	CQ0402BRNPO9BN4R0	0402	NPO	4.0pF	50 V	±0.1pF
3	CQ0402BRNPO9BNR40	0402	NPO	0.4pF	50 V	±0.1pF	25	CQ0402CRNPO9BN5R0	0402	NPO	5.0pF	50 V	±0.25pF
4	CQ0402BRNPO9BNR50	0402	NPO	0.5pF	50 V	±0.1pF	26	CQ0402CRNPO9BN5R6	0402	NPO	5.6pF	50 V	±0.25pF
5	CQ0402BRNPO9BNR60	0402	NPO	0.6pF	50 V	±0.1pF	27	CQ0402CRNPO9BN6R0	0402	NPO	6.0pF	50 V	±0.25pF
6	CQ0402BRNPO9BNR70	0402	NPO	0.7pF	50 V	±0.1pF	28	CQ0402CRNPO9BN6R2	0402	NPO	6.2pF	50 V	±0.25pF
7	CQ0402BRNPO9BNR80	0402	NPO	0.8pF	50 V	±0.1pF	29	CQ0402CRNPO9BN6R0	0402	NPO	6.0pF	50 V	±0.25pF
8	CQ0402BRNPO9BNR90	0402	NPO	0.9pF	50 V	±0.1pF	30	CQ0402CRNPO9BN6R2	0402	NPO	6.2pF	50 V	±0.25pF
9	CQ0402BRNPO9BN1R0	0402	NPO	1.0pF	50 V	±0.1pF	31	CQ0402CRNPO9BN6R8	0402	NPO	6.8pF	50 V	±0.25pF
10	CQ0402BRNPO9BN1R1	0402	NPO	1.1pF	50 V	±0.1pF	32	CQ0402CRNPO9BN7R0	0402	NPO	7.0pF	50 V	±0.25pF
11	CQ0402BRNPO9BN1R2	0402	NPO	1.2pF	50 V	±0.1pF	33	CQ0402CRNPO9BN7R5	0402	NPO	7.5pF	50 V	±0.25pF
12	CQ0402BRNPO9BN1R3	0402	NPO	1.3pF	50 V	±0.1pF	34	CQ0402CRNPO9BN8R0	0402	NPO	8.0pF	50 V	±0.25pF
13	CQ0402BRNPO9BN1R5	0402	NPO	1.5pF	50 V	±0.1pF	35	CQ0402CRNPO9BN8R2	0402	NPO	8.2pF	50 V	±0.25pF
14	CQ0402BRNPO9BN1R6	0402	NPO	1.6pF	50 V	±0.1pF	36	CQ0402CRNPO9BN9R0	0402	NPO	9.0pF	50 V	±0.25pF
15	CQ0402BRNPO9BN1R8	0402	NPO	1.8pF	50 V	±0.1pF	37	CQ0402CRNPO9BN9R1	0402	NPO	9.1pF	50 V	±0.25pF
16	CQ0402BRNPO9BN2R0	0402	NPO	2.0pF	50 V	±0.1pF	38	CQ0402JRNPO9BN100	0402	NPO	10pF	50 V	±5%
17	CQ0402BRNPO9BN2R2	0402	NPO	2.2pF	50 V	±0.1pF	39	CQ0402JRNPO9BN120	0402	NPO	12pF	50 V	±5%
18	CQ0402BRNPO9BN2R4	0402	NPO	2.4pF	50 V	±0.1pF	40	CQ0402JRNPO9BN150	0402	NPO	15pF	50 V	±5%
19	CQ0402BRNPO9BN2R7	0402	NPO	2.7pF	50 V	±0.1pF	41	CQ0402JRNPO9BN180	0402	NPO	18pF	50 V	±5%
20	CQ0402BRNPO9BN3R0	0402	NPO	3.0pF	50 V	±0.1pF	42	CQ0402JRNPO9BN220	0402	NPO	22pF	50 V	±5%
21	CQ0402BRNPO9BN3R3	0402	NPO	3.3pF	50 V	±0.1pF	43	CQ0402JRNPO9BN270	0402	NPO	27pF	50 V	±5%
22	CQ0402BRNPO9BN3R6	0402	NPO	3.6pF	50 V	±0.1pF	44	CQ0402JRNPO9BN330	0402	NPO	33pF	50 V	±5%

Pieces per items: Case size 01005 to 0402, 80pcs; 0603 to 1808, 40pcs; 1812, 20pcs.