

Surface-mount Ceramic Multilayer Capacitors (RoHS compliant & Halogen Free)

CQ0805000000SB000

Hi-Frequency 0805 Sample Kit

Spec Sheet

Scope

This product specification is applied to Multi-layer Ceramic Capacitor used for High Frequency application .



No.	Part. NO.	Size	TC	Cap.	Volt.	Tol	No.	Part. NO.	Size	TC	Cap.	Volt.	Tol
1	CQ0805BRNPOYBNR20	0805	NPO	0.2pF	250 V	±0.1pF	24	CQ0805BRNPOYBN4R7	0805	NPO	4.7pF	250 V	±0.1pF
2	CQ0805BRNPOYBNR30	0805	NPO	0.3pF	250 V	±0.1pF	25	CQ0805CRNPOYBN5R6	0805	NPO	5.6pF	250 V	±0.25pF
3	CQ0805BRNPOYBNR40	0805	NPO	0.4pF	250 V	±0.1pF	26	CQ0805CRNPOYBN6R2	0805	NPO	6.2pF	250 V	±0.25pF
4	CQ0805BRNPOYBNR50	0805	NPO	0.5pF	250 V	±0.1pF	27	CQ0805CRNPOYBN6R8	0805	NPO	6.8pF	250 V	±0.25pF
5	CQ0805BRNPOYBNR60	0805	NPO	0.6pF	250 V	±0.1pF	28	CQ0805CRNPOYBN7R0	0805	NPO	7.0pF	250 V	±0.25pF
6	CQ0805BRNPOYBNR70	0805	NPO	0.7pF	250 V	±0.1pF	29	CQ0805CRNPOYBN7R5	0805	NPO	7.5pF	250 V	±0.25pF
7	CQ0805BRNPOYBNR80	0805	NPO	0.8pF	250 V	±0.1pF	30	CQ0805CRNPOYBN8R0	0805	NPO	8.0pF	250 V	±0.25pF
8	CQ0805BRNPOYBNR90	0805	NPO	0.9pF	250 V	±0.1pF	31	CQ0805CRNPOYBN8R2	0805	NPO	8.2pF	250 V	±0.25pF
9	CQ0805BRNPOYBN1R0	0805	NPO	1.0pF	250 V	±0.1pF	32	CQ0805CRNPOYBN9R0	0805	NPO	9.0pF	250 V	±0.25pF
10	CQ0805BRNPOYBN1R1	0805	NPO	1.1pF	250 V	±0.1pF	33	CQ0805CRNPOYBN9R1	0805	NPO	9.1pF	250 V	±0.25pF
11	CQ0805BRNPOYBN1R2	0805	NPO	1.2pF	250 V	±0.1pF	34	CQ0805JRNPOYBN100	0805	NPO	10pF	250 V	±5%
12	CQ0805BRNPOYBN1R3	0805	NPO	1.3pF	250 V	±0.1pF	35	CQ0805JRNPOYBN120	0805	NPO	12pF	250 V	±5%
13	CQ0805BRNPOYBN1R5	0805	NPO	1.5pF	250 V	±0.1pF	36	CQ0805JRNPOYBN150	0805	NPO	15pF	250 V	±5%
14	CQ0805BRNPOYBN1R6	0805	NPO	1.6pF	250 V	±0.1pF	37	CQ0805JRNPOYBN180	0805	NPO	18pF	250 V	±5%
15	CQ0805BRNPOYBN1R8	0805	NPO	1.8pF	250 V	±0.1pF	38	CQ0805JRNPOYBN220	0805	NPO	22pF	250 V	±5%
16	CQ0805BRNPOYBN2R0	0805	NPO	2.0pF	250 V	±0.1pF	39	CQ0805JRNPOYBN270	0805	NPO	27pF	250 V	±5%
17	CQ0805BRNPOYBN2R2	0805	NPO	2.2pF	250 V	±0.1pF	40	CQ0805JRNPOYBN330	0805	NPO	33pF	250 V	±5%
18	CQ0805BRNPOYBN2R4	0805	NPO	2.4pF	250 V	±0.1pF	41	CQ0805JRNPOYBN470	0805	NPO	47pF	250 V	±5%
19	CQ0805BRNPOYBN2R7	0805	NPO	2.7pF	250 V	±0.1pF	42	CQ0805JRNPOYBN560	0805	NPO	56pF	250 V	±5%
20	CQ0805BRNPOYBN3R3	0805	NPO	3.3pF	250 V	±0.1pF	43	CQ0805JRNPOYBN680	0805	NPO	68pF	250 V	±5%
21	CQ0805BRNPOYBN3R6	0805	NPO	3.6pF	250 V	±0.1pF	44	CQ0805JRNPOYBN820	0805	NPO	82pF	250 V	±5%
22	CQ0805BRNPOYBN3R9	0805	NPO	3.9pF	250 V	±0.1pF	45	CQ0805JRNPOYBN101	0805	NPO	100pF	250 V	±5%
23	CQ0805BRNPOYBN4R3	0805	NPO	4.3pF	250 V	±0.1pF							

Piecs per items: Case size 01005 to 0402, 80pcs; 0603 to 1808, 40pcs; 1812, 20pcs.