



Part Number : [2249340004](#)

Series Number : 224934

Product Category : Terminal Blocks and Barrier Strip

Product Description : 15.00mm Pitch Lever Activated Fixed Mount PCB Terminal Block, 35° Wire Entry, Left Rear Terminal, 4 Circuits

Status : Active

Engineering Number : MX-TLM-705AA-15-04

Documents & Resources

Drawings

[Drawing 2249340004_sd.pdf](#)

3D Models and Design Files


[3D Model 2249340004_stp.zip](#)

Specifications

[Packaging Specification 1302270418-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	224934
Description	15.00mm Pitch Lever Activated Fixed Mount PCB Terminal Block, 35° Wire Entry, Left Rear Terminal, 4 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Family	Terminal Blocks & Barrier Strips
Product Name	Lever Activated Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	196823649608

Electrical

Current - Maximum per Contact	66.0A
Voltage - Maximum	600V

Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Green
Entry Angle	35° Angle
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide
Net Weight	3.900/kg
Number of Rows	1

Orientation	Vertical
Panel Mount	No
PC Tail Length	3.60mm
PCB Thickness - Recommended	2.00mm
Pitch - Mating Interface	15.00mm
Pitch - Termination Interface	15.00mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +115°C
Termination Interface Style	Through Hole
Wire Size (AWG)	4, 6, 8, 10, 12, 14, 16, 18
Wire Size mm ²	1.24-5.89

This document was generated on Aug 27, 2024