

M17 Crimp Contact 1,0mm,male,0,25-0,5mm²



Image is for illustration purposes only. Please refer to product description.

Part number	21 17 067 0000
Specification	M17 Crimp Contact 1,0mm,male,0,25-0,5mm ²
HARTING eCatalogue	https://b2b.harting.com/21170670000

Identification

Category	Contacts
Series	Circular connectors M17
Type of contact	Crimp contact

Version

Gender	Male
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.25 ... 0.5 mm ²
Conductor cross-section [AWG]	AWG 24 ... AWG 20
Stripping length	5 mm
Limiting temperature	-40 ... +125 °C

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Gold plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances Not contained

Commercial data

Packaging size	100
Net weight	0.3 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140568679
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors