

20V MAX* Cordless Drill | Driver

BCD702C1



The BLACK+DECKER® 20V MAX* cordless drill/driver offers an 11-position clutch and maximize torque. An integrated LED light and built-in bit storage is included.

Our 20V MAX* Cordless Drill/Driver features the power and versatility to handle a wide variety of household DIY tasks. 20V MAX* power delivers the torque and speed you need with runtime to keep going. The 11-position clutch enhances control to prevent stripping screws in Driver mode. In Drill mode, the transmission is opened to maximize torque. An integrated LED lights your way in poorly lit work areas. Built-in fastening bit storage keeps them on hand and organized.

- 11-position clutch of this cordless drill helps to prevent stripping screws

- Power drill with 20V MAX** Lithium Ion battery for excellent power and runtime
- The drill/driver has integrated LED light to help provide illumination
- Built-in driver bit holder for storage and organization
- Part of 20V MAX** System. Maximum initial battery voltage (measured without workload) is 20V MAX*. Nominal voltage is 18 volts

Specs & Parts:

App Compatibility: No

Battery Included: Yes

Battery Qty: 1

Battery Type: 20V MAX* Lithium Ion

Battery Warranty: 2-year limited

Battery Amp Hours: 1.5 Ah

Charger Included: Yes

Charger Type: Wall Mountable Charging Base

Charge Time: 225

Chuck Size: 3/8 in

Chuck Type: Keyless

Cordless vs Corded: Cordless

GTIN: 00885911554022

Max RPM: 600 RPM

Motor Type: Brushed

No. of Batteries Required: 1

Power Type: ELECTRICITY

Product Application: Drilling

Height: 8.4 IN

Length: 10.9 IN

Weight: 3.3 LB

Width: 2.8 IN

Voltage: 20 V

Watt Hours: 30

Warranty: 1 Year Limited Warranty

Includes: (1) Lbxr20 20V Max* Battery. (1) Lcs1620 Charger. (1) Bcd702 20V Max* Drill Driver