


**RoHS
Compliant**




Description

These high quality, easy to use nylon non-releasable cable ties are available in a range of sizes and can effectively bundle cables together as well as a multitude of other applications.

Specifications

Thickness : 0.9mm
 Material : Nylon 66
 Flammability : 94V-2 to UL standard
 Operating Temperature : -40°C to +85°C

Diagram



Part Number Table

Description	External Width	External Length	Max. Bundle Dia.	Min. Loop Tensile Strength		Colour	Package	Part Number
	(mm)	(mm)	(mm)	(lbs)	(kgs)		(Pcs)	
Cable Tie, Nylon 66	1.8	100	22	14	6.5	Natural	100	PEL01458
	1.8	100	22	14	6.5	Black	100	PEL01459
	2.5	60	11	18	8	Natural	100	PEL01460
	2.5	60	11	18	8	Black	100	PEL01461
	2.5	80	16	18	8	Natural	100	PEL01462
	2.5	80	16	18	8	Black	100	PEL01463
	2.5	100	22	18	8	Natural	100	PEL01464
	2.5	100	22	18	8	Natural	1000	PEL01465
	2.5	100	22	18	8	Black	100	PEL01466
	2.5	100	22	18	8	Black	1000	PEL01467
	2.5	120	28	18	8	Natural	100	PEL01468

Nylon Cable Ties



Description	External Width	External Length	Max. Bundle Dia.	Min. Loop Tensile Strength		Colour	Package	Part Number
	(mm)	(mm)	(mm)	(lbs)	(kgs)		(Pcs)	
Cable Tie, Nylon 66	2.5	120	28	18	8	Black	100	PEL01469
	2.5	140	33	18	8	Natural	100	PEL01470
	2.5	140	33	18	8	Natural	1000	PEL01471
	2.5	140	33	18	8	Black	100	PEL01472
	2.5	140	33	18	8	Black	1000	PEL01473
	2.5	150	35	18	8	Natural	100	PEL01474
	2.5	150	35	18	8	Black	100	PEL01475
	2.5	160	40	18	8	Natural	100	PEL01476
	2.5	160	40	18	8	Black	100	PEL01477
	2.5	200	53	18	8	Natural	100	PEL01478
	2.5	200	53	18	8	Natural	1000	PEL01479
	2.5	200	53	18	8	Black	100	PEL01480
	2.5	200	53	18	8	Black	1000	PEL01481
	2.7	250	65	33	15	Natural	100	PEL01482
	2.7	250	65	33	15	Black	100	PEL01483
	3.2	150	35	40	18	Natural	100	PEL01484
	3.2	150	35	40	18	Natural	1000	PEL01485
	3.2	150	35	40	18	Black	100	PEL01486
	3.2	150	35	40	18	Black	1000	PEL01487
	3.6	120	30	40	18	Natural	100	PEL01488
	3.6	120	30	40	18	Black	100	PEL01489
	3.6	150	35	40	18	Natural	100	PEL01490
	3.6	150	35	40	18	Black	100	PEL01491
	3.6	200	53	40	18	Natural	100	PEL01492
	3.6	200	53	40	18	Natural	1000	PEL01493
	3.6	200	53	40	18	Black	100	PEL01494
	3.6	200	53	40	18	Black	1000	PEL01495
	3.6	220	58	40	18	Natural	100	PEL01496
	3.6	220	58	40	18	Black	100	PEL01497
	3.6	250	65	40	18	Natural	100	PEL01498
3.6	250	65	40	18	Black	100	PEL01499	
3.6	280	70	40	18	Natural	100	PEL01500	
3.6	280	70	40	18	Black	100	PEL01501	
3.6	300	80	40	18	Natural	100	PEL01502	
3.6	300	80	40	18	Natural	1000	PEL01503	
3.6	300	80	40	18	Black	100	PEL01504	

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands



Nylon Cable Ties



Description	External Width	External Length	Max. Bundle Dia.	Min. Loop Tensile Strength		Colour	Package	Part Number
	(mm)	(mm)	(mm)	(lbs)	(kgs)		(Pcs)	
Cable Tie, Nylon 66	3.6	300	80	40	18	Black	1000	PEL01505
	3.6	370	102	40	18	Natural	100	PEL01506
	3.6	370	102	40	18	Black	100	PEL01507
	4.6	120	26	50	22	Black	100	PEL01508
	4.6	120	26	50	22	Natural	100	PEL01509
	4.6	160	39	50	22	Natural	1000	PEL01510
	4.6	160	39	50	22	Natural	100	PEL01511
	4.6	160	39	50	22	Black	1000	PEL01512
	4.6	160	39	50	22	Black	100	PEL01513
	4.6	180	46	50	22	Natural	100	PEL01514
	4.6	180	46	50	22	Natural	1000	PEL01515
	4.6	180	46	50	22	Black	100	PEL01516
	4.6	180	46	50	22	Black	1000	PEL01517
	4.6	200	53	50	22	Black	100	PEL01518
	4.6	200	53	50	22	Black	1000	PEL01519
	4.6	200	53	50	22	Natural	100	PEL01520
	4.6	200	53	50	22	Natural	1000	PEL01521
	4.6	250	65	50	22	Natural	100	PEL01522
	4.6	250	65	50	22	Black	100	PEL01523
	4.6	280	70	50	22	Natural	100	PEL01524
	4.6	280	70	50	22	Black	100	PEL01525
	4.6	300	82	50	22	Natural	100	PEL01526
	4.6	300	82	50	22	Natural	1000	PEL01527
	4.6	300	82	50	22	Black	100	PEL01528
	4.6	300	82	50	22	Black	1000	PEL01529
	4.8	350	90	50	22	Natural	100	PEL01530
	4.8	350	90	50	22	Black	100	PEL01531
	4.8	380	105	50	22	Natural	100	PEL01532
	4.8	380	105	50	22	Natural	1000	PEL01533
	4.8	380	105	50	22	Black	100	PEL01534
	4.8	380	105	50	22	Black	1000	PEL01535
	4.8	400	108	50	22	Black	100	PEL01536
4.8	400	108	50	22	Natural	100	PEL01537	
4.8	430	115	50	22	Natural	100	PEL01538	
4.8	430	115	50	22	Black	100	PEL01539	
4.8	450	130	50	22	Natural	100	PEL01540	



Nylon Cable Ties



Description	External Width	External Length	Max. Bundle Dia.	Min. Loop Tensile Strength		Colour	Package	Part Number
	(mm)	(mm)	(mm)	(lbs)	(kgs)		(Pcs)	
Cable Tie, Nylon 66	4.8	450	130	50	22	Black	100	PEL01541
	4.8	500	150	50	22	Black	100	PEL01542
	4.8	500	150	50	22	Natural	100	PEL01543
	6.8	180	42	85	38	Natural	100	PEL01544
	6.8	180	42	85	38	Black	100	PEL01545
	6.8	200	50	85	38	Black	100	PEL01546
	6.8	200	50	85	38	Natural	100	PEL01547
	7.6	200	50	120	55	Natural	100	PEL01548
	7.6	200	50	120	55	Black	100	PEL01549
	7.6	250	63	120	55	Natural	100	PEL01550
	7.6	250	63	120	55	Black	100	PEL01551
	7.6	300	80	120	55	Natural	100	PEL01552
	7.6	300	80	120	55	Black	100	PEL01553
	7.6	350	90	120	55	Natural	100	PEL01554
	7.6	350	90	120	55	Black	100	PEL01555
	7.6	370	98	120	55	Natural	100	PEL01556
	7.6	370	98	120	55	Black	100	PEL01557
	7.6	400	105	120	55	Natural	100	PEL01558
	7.6	400	105	120	55	Black	100	PEL01559
	7.6	450	125	120	55	Natural	100	PEL01560
	7.6	450	125	120	55	Black	100	PEL01561
	7.6	500	145	120	55	Natural	100	PEL01562
	7.6	500	145	120	55	Black	100	PEL01563
	7.6	550	160	120	55	Natural	100	PEL01564
	7.6	550	160	120	55	Black	100	PEL01565
	7.6	600	170	120	55	Natural	100	PEL01566
	7.6	600	170	120	55	Black	100	PEL01567
	7.6	650	190	120	55	Natural	100	PEL01568
	7.6	650	190	120	55	Black	100	PEL01569
	7.6	750	220	120	55	Natural	100	PEL01570
7.6	750	220	120	55	Black	100	PEL01571	
9	450	120	175	80	Natural	100	PEL01572	
9	450	120	175	80	Black	100	PEL01573	
9	550	160	175	80	Natural	100	PEL01574	
9	550	160	175	80	Black	100	PEL01575	
9	650	190	175	80	Natural	100	PEL01576	

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands



Nylon Cable Ties



Description	External Width	External Length	Max. Bundle Dia.	Min. Loop Tensile Strength		Colour	Package	Part Number
	(mm)	(mm)	(mm)	(lbs)	(kgs)		(Pcs)	
Cable Tie, Nylon 66	9	650	190	175	80	Black	100	PEL01577
	9	700	205	175	80	Natural	100	PEL01578
	9	700	205	175	80	Black	100	PEL01579
	9	920	265	175	80	Natural	50	PEL01580
	9	920	265	175	80	Black	50	PEL01581
	9	1020	295	175	80	Natural	50	PEL01582
	9	1020	295	175	80	Black	50	PEL01583
	12.7	400	105	250	114	Black	100	PEL01584
	12.7	400	105	250	114	Natural	100	PEL01585
	12	650	190	250	114	Natural	100	PEL01586
	12	650	190	250	114	Black	100	PEL01587

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
 Farnell.com/exclusive-brands
 Element14.com/exclusive-brands

