



## **Pan-Ty® PLT1M-M0 Cable Tie, Black, UV PA6.6, 3.9"L, 18lb, PK1000**

PLT1M-M0

Panduit PLT1M-M0 Locking Cable Ties are designed to satisfy the needs of general applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Miniature cross section, 3.9" (99mm) length. For Indoor/Outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 1000.

### **Specifications**

|                                       |  |
|---------------------------------------|--|
| Product Type                          | Premium Cable Tie  |
| Color                                 | Black  |
| Environment                           | Indoor/Outdoor   |
| Material                              | Nylon 6.6  |
| Resistance Properties                 | UV-Resistant, Weather-Resistant  |
| Overall Length (In.)                  | 3.9  |
| Overall Length (mm)                   | 99   |
| Body Width (In.)                      | 0.098  |
| Body Width (mm)                       | 2.5  |
| Body Thickness (In.)                  | 0.043  |
| Body Thickness (mm)                   | 1.1  |
| Maximum Bundle Diameter (In.)         | 0.87   |
| Maximum Bundle Diameter (mm)          | 22   |
| Minimum Bundle Diameter (In.)         | 0.06   |
| Minimum Bundle Diameter (mm)          | 1.5  |
| Minimum Loop Tensile Strength (N)     | 80   |
| Minimum Loop Tensile Strength (lb)    | 18   |
| Maximum Operating Temperature (°C)    | 85   |
| Maximum Operating Temperature (°F)    | 185  |
| Minimum Operating Temperature (°C)    | -60  |
| Minimum Operating Temperature (°F)    | -76  |
| Minimum Installation Temperature (°C) | -20  |
| Minimum Installation Temperature (°F) | -4   |
| Standards Met                         | CSA Certified, UL Recognized (File #E56854), UL 62275 Compliant (Type 2, 21), RoHS Compliant |
| For Use With                          | GTS-E, GS2B-E, PTS, PPTS, STS2   |

**Specifications (continued)**

|               |  |
|---------------|--|
| Part Features | One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength. |
|---------------|--|

**Packaging Detail**

|                       |             |
|-----------------------|-------------|
| UPC                   | 07498354958 |
| Std. Pkg. Qty.        | 1000        |
| Std. Pkg. Volume (cf) | 0.0628      |
| Std. Ctn. Qty.        | 50000       |
| Std. Ctn. Volume (cf) | 3.1414      |