



Pan-Ty® PLT.7M-M Cable Tie, PA6.6, 3.1"L, 18lb, PK1000

PLT.7M-M

Panduit PLT.7M-M Locking Cable Ties are designed to satisfy the needs of general applications, while delivering consistent performance and reliability. Featuring a curved tip to allow for easy pick up from flat surfaces and faster initial threading. Miniature cross section, 3.1" (79mm) length. Made of Nylon 6.6, are natural in color and come in packages of 1000.

Specifications

Product Type	Premium Cable Tie
Color	Natural
Environment	Indoor
Material	Nylon 6.6
Overall Length (In.)	3.1
Overall Length (mm)	79
Body Width (In.)	0.09
Body Width (mm)	2.3
Body Thickness (In.)	0.032
Body Thickness (mm)	0.8
Maximum Bundle Diameter (In.)	0.68
Maximum Bundle Diameter (mm)	17
Minimum Bundle Diameter (In.)	0.03
Minimum Bundle Diameter (mm)	0.8
Minimum Loop Tensile Strength (N)	80
Minimum Loop Tensile Strength (lb)	18
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Installation Temperature (°C)	-20
Minimum Installation Temperature (°F)	-4
Standards Met	UL Recognized (File #E56854), UL 62275 Compliant (Type 2, 21), RoHS Compliant
Military Cross Reference Number	MS3367-4-9
For Use With	GTS-E, GS2B-E, PTS, PPTS, STS2
Part Features	One-piece locking wedge for consistent performance and reliability. Low thread force and high loop tensile strength.

Packaging Detail

UPC	07498352600
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.0361
Std. Ctn. Qty.	50000
Std. Ctn. Volume (cf)	1.8029