



Pan-Ty® PLWP1SB-D Wing Push Mount Cable Tie, PA6.6, .187" Hole Dia., 5.2"L

PLWP1SB-D

Panduit PLWP1SB-D Locking Wing Mount Push Ties use an all-in-one design to attach bundles to another surface using a stable, secure, rattle-free installation. Standard cross section, 5.2" (132mm) length. For indoor use, made of Nylon 6.6, are natural in color and come in packages of 500.

Specifications

Product Type	Premium Cable Tie
Color	Natural
Environment	Indoor
Material	Nylon 6.6
Overall Length (In.)	5.2
Overall Length (mm)	132
Body Width (In.)	0.19
Body Width (mm)	4.8
Body Thickness (In.)	0.052
Body Thickness (mm)	1.3
Maximum Bundle Diameter (In.)	1
Maximum Bundle Diameter (mm)	25.4
Minimum Bundle Diameter (In.)	0.06
Minimum Bundle Diameter (mm)	1.5
Minimum Loop Tensile Strength (N)	222
Minimum Loop Tensile Strength (lb)	50
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Minimum Installation Temperature (°C)	-20
Minimum Installation Temperature (°F)	-4
Standards Met	UL Recognized (File #E56854), RoHS Compliant
For Use With	GTS-E, GS2B-E, GTH-E, GS4H-E, PTS, PTH, PPTS, STS2, STH2
Part Features	Cable tie, mount and fastener in a single part. Used to attach bundles to another surface. Anchor is easily pressed into a preformed hole and locks in place.

Packaging Detail

UPC	07498354342
Std. Pkg. Qty.	500
Std. Pkg. Volume (cf)	0.2003
Std. Ctn. Qty.	5000
Std. Ctn. Volume (cf)	2.0027