



StrongHold™ S12-50-M Cable Tie, Natural, PA 6.6, 50lb Min Loop Tensile, 11.81"

S12-50-M

The S12-50-M StrongHold Cable Ties offers contractors an economical cable tie option for commercial construction and general-purpose applications. Standard, 11.81" (300mm) length, made of Nylon 6.6, AH-2 Plenum rated, are natural in color and come in packages of 1000.

Specifications

Product Type	Cable Tie
Sub Brand	StrongHold™
Color	Natural
Environment	Plenum
Material	Nylon 6.6
Overall Length (In.)	11.81
Overall Length (mm)	300
Body Width (In.)	0.19
Body Width (mm)	4.8
Body Thickness (In.)	0.051
Body Thickness (mm)	1.3
Maximum Bundle Diameter (In.)	2.99
Maximum Bundle Diameter (mm)	76
Minimum Bundle Diameter (In.)	0.12
Minimum Bundle Diameter (mm)	3
Minimum Loop Tensile Strength (N)	222
Minimum Loop Tensile Strength (lb)	50
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-40
Minimum Operating Temperature (°F)	-40
Standards Met	UL 62275 Compliant (Type 2, 21), RoHS Compliant

Packaging Detail

UPC	61305625811
Std. Pkg. Qty.	1000
Std. Pkg. Volume (cf)	0.3516
Std. Ctn. Qty.	5000
Std. Ctn. Volume (cf)	1.7578