



StrongHold™ S15-50-C0 Cable Tie, Black, PA 6.6, 50lb Min Loop Tensile, 14.57"

S15-50-C0

The S15-50-C0 StrongHold Cable Ties offers contractors an economical cable tie option for commercial construction and general-purpose applications. Standard, 14.57" (370mm) length and are AH-2 Plenum rated. For outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 100.

Specifications

Product Type	Cable Tie
Sub Brand	StrongHold™
Color	Black
Environment	Plenum
Material	Nylon 6.6
Resistance Properties	UV-Resistant
Overall Length (In.)	14.57
Overall Length (mm)	370
Body Width (In.)	0.19
Body Width (mm)	4.8
Body Thickness (In.)	0.051
Body Thickness (mm)	1.3
Maximum Bundle Diameter (In.)	4.02
Maximum Bundle Diameter (mm)	102
Minimum Bundle Diameter (In.)	0.12
Minimum Bundle Diameter (mm)	3
Minimum Loop Tensile Strength (N)	222
Minimum Loop Tensile Strength (lb)	50
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Operating Temperature (°C)	-40
Minimum Operating Temperature (°F)	-40
Standards Met	UL 62275 Compliant (Type 2, 21), RoHS Compliant

Packaging Detail

UPC	61305625817
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0352
Std. Ctn. Qty.	1000
Std. Ctn. Volume (cf)	0.3522