



Part No. CS1206KKX7R9BB334

| 1206 (3216) | X7R | 50 Vdc | 330 nF | ±10% |

Surface-Mount Ceramic Multilayer Capacitors (RoHS compliant & Halogen Free)

■ Appearance



■ Dimension (mm)

L (Length)	3.20 ±0.40
W (width)	1.60 ±0.20
T (Thickness)	1.60 ±0.20
L2/L3	0.25~0.85
L4	1.5

■ Specification

Application	Boardflex Sensitive
Case Size (EIA/JIS)	1206 (3216)
Temperature Characteristic	X7R
Operation Temp. Range	-55 to +125°C
Capacitance	330 nF
Capacitance Tolerance	±10%
Rated Voltage (VDC)	50
Endurance (% Rated voltage)	200%
Tanδ (max)	2.50%
Insulation Resistance (min)	303 MΩ
Packing	Embossed Plastic Tape Reel 7 inch
Standard Packing Qty (pcs)	2,000
Test Method	IEC-60384





The data are for reference only. Electrical characteristics vary depending on environment or measurement condition.

YAGEO reserves the right to make change to the data at any time without notice. Before making final selection, please check product specification.

Part No. CS1206KKX7R9BB334

| 1206 (3216) | X7R | 50 Vdc | 330 nF | ±10% |

Surface-Mount Ceramic Multilayer Capacitors (RoHS compliant & Halogen Free)







The data are for reference only. Electrical characteristics vary depending on environment or measurement condition. YAGEO reserves the right to make change to the data at any time without notice. Before making final selection, please check product specification.

Part No. CS1206KKX7R9BB334

| 1206 (3216) | X7R | 50 Vdc | 330 nF | ±10% |

Surface-Mount Ceramic Multilayer Capacitors (RoHS compliant & Halogen Free)



The data are for reference only. Electrical characteristics vary depending on environment or measurement condition. YAGEO reserves the right to make change to the data at any time without notice. Before making final selection, please check product specification.

