

Product data sheet

Characteristics

CP12036LI

APC Back-UPS Connect 12Vdc 36W, lithium-ion, mini network ups to protect internet routers, IP cameras and more



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	12 V DC
Product or component type	Uninterruptible power supply (UPS)
Output voltage	12 V DC
Battery type	Li-Ion (Lithium-Ion)

Complementary

Number of tare power	2 W
----------------------	-----

Batteries & Runtime

Battery recharge time	9 H
-----------------------	-----

Physical

Colour	White
Width	99 Mm
Depth	109 Mm
Net weight	300 G
Mounting mode	Not rack-mountable
Height	25 Mm

Output

Maximum configurable power in W	36 W
Output voltage	12 V

Conformance

Product certifications	CE
Standards	CE EN/IEC 61000-4-8 EN/IEC 61000-4-2 EN/IEC 62368-1

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-10...50 °C
Storage altitude	0...5000 M
IP degree of protection	< IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.300 Cm
Package 1 Width	11.500 Cm
Package 1 Length	16.300 Cm
Package 1 Weight	366.000 G
Unit Type of Package 2	S02
Number of Units in Package 2	10
Package 2 Height	15.000 Cm
Package 2 Width	30.000 Cm
Package 2 Length	40.000 Cm
Package 2 Weight	3.900 Kg
SCC14	10731304632396

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Logistical informations

Country of origin	CN
-------------------	----

Contractual warranty

Warranty	24 months
----------	-----------

Product Life Status : **Commercialised**