



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Main Input Voltage	230 V
Output voltage	230 V
Rated power in W	450 W
Rated power in VA	800 VA
Product or component type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 60320 C14
Output connection type	6 IEC 60320 C13
Cable length	1.50 M
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	User manual

## Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	8 H
Battery voltage	12 V
Battery capacity	7.0 Ah
Battery life	3...5 Year(S)
Extended runtime	0

## General

Number of power module free slots	0
Number of power module filled slots	0
Redundant	No
UPS size	WS

## Physical

Colour	Black
Height	9.25 Cm
Width	16.05 Cm
Depth	30.5 Cm
Net weight	5.3 Kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	No

## Input

Network frequency	50/60 Hz +/- 5 Hz auto-sensing
Input voltage limits	170...280 V

## Output

Maximum configurable power in W	450 W
Output frequency	50/60 Hz +/- 1 Hz unsynchronised
UPS type	Line interactive
Wave type	Stepped approximation to a sine wave
Graph display	1
Maximum configurable power in VA	800 VA
Transfer time	6 ms typical : 10 ms maximum

## Conformance

Product certifications	CE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...90 %
Operating altitude	0...6667 ft
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...90 %
Storage altitude	0.0000000000...15240.0000000000 M
Acoustic level	40 dBA
IP degree of protection	IP20

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous-tone alarm
-------	--

## Surge Protection and Filtering

Surge energy rate	156 J
-------------------	-------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	23.7 Cm
Package 1 Width	37.3 Cm
Package 1 Length	14.3 Cm

Package 1 Weight	5.6 Kg
SCC14	10731304338342

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

### Logistical informations

Country of origin	AE
-------------------	----

### Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status :	<b>Commercialised</b>
-----------------------	-----------------------