

• APTIV •



36 Way F Hybrid 1.5 2.8 SICMA Inline Unsealed Connector Black

Part: 13651269

Attributes

Product Family: SICMA

Product Series: Inline Unsealed Connector

Max. operating temperature: +125°C

Min. operating temperature: -40°C

No. of Ways: 36

Gender: Female

Length (mm): 28.3

Width (mm): 84.7

Height (mm): 30.2

Color: BLACK

Primary Locking Mechanism: CAVITY LOCK

Weight (g): 27

Terminal 1 Size: 1.5

Terminal 2 Size: 2.8

Sealing: Unsealed

Primary Material: PBT

Vibration Rating: 3G