



64 Way F Hybrid 0.64 1.5 CMC Sealed Connector Black

Part Number: 13648596

Product Family: CMC

Product Series: 48 Way Series

Max. operating temperature: +125°C

Min. operating temperature: -40°C

No. of Ways: 64

Gender: Female

Length (mm): 36

Width (mm): 61.75

Height (mm): 39.5

Color: BLACK

Primary Locking Mechanism: LOCKING LANCE

Weight (g): 44.54

Terminal 1 Size: 0.64

Terminal 2 Size: 1.5

Sealing: Sealed

Primary Material: PBT GF 15

Sealing Rating: IPX9K

Vibration Rating: V2