







**This item includes:**

			
<b>Item No.: 221-412</b> Splicing connector with levers; for all conductor types; max. 4 mm <sup>2</sup> ; 2-conductor; with levers; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm <sup>2</sup> ; transparent	<b>Item No.: 221-413</b> Splicing connector with levers; for all conductor types; max. 4 mm <sup>2</sup> ; 3-conductor; with levers; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm <sup>2</sup> ; transparent	<b>Item No.: 221-415</b> Splicing connector with levers; for all conductor types; max. 4 mm <sup>2</sup> ; 5-conductor; with levers; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm <sup>2</sup> ; transparent	<b>Item No.: 221-2411</b> Inline splicing connector with levers; for all conductor types; max. 4 mm <sup>2</sup> ; 2-conductor; transparent housing; Transparent cover; Surrounding air temperature: max 85°C (T85); 4,00 mm <sup>2</sup> ; transparent
		<b>8</b>	<b>30</b>

**Notes**

Safety management note

**NOTICE: Observe installation and safety instructions!**

- **Only to be used by electricians!**
- Do not work under voltage/load!
- Use only for proper use!
- Observe national regulations/standards/guidelines!
- Observe technical specifications for the products!
- Observe the number of permissible potentials!
- Do not use damaged/dirty components!
- Observe conductor types, cross-sections and strip lengths!
- Insert conductor until it hits the product's backstop!
- Use original accessories!

**To be sold only with installation instructions!**

**Physical data**

Width	259 mm / 10.197 inches
Height	42 mm / 1.653 inches
Depth	106 mm / 4.173 inches

**Material data**

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Fire load	5.582 MJ
Weight	412.1 g

**Commercial data**

ETIM 9.0	EC000446
ETIM 8.0	EC000446
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4066966194883
Customs tariff number	85369010000

**Environmental Product Compliance**

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

**Downloads**

**Environmental Product Compliance**

<b>Compliance Search</b>	
Environmental Product Compliance 887-803	