

Product Datasheet

Product code: **PC170WE**

Product type: TEK-ME Carbon Steel Hand tools

Made in: Italy

Description: The PC170WE is a flush cutter. Its medium size (2,5mm thick) allow the cutting of bigger electronic components than in the micro line. This cutter is specially designed to reduce cutting effort while maintaining the same characteristics of PC25. The cutters are equipped with an ESD and ergonomic handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharges. The blades are also equipped with a lead catcher safety clip.

Head description: Angled Medium, Shear

Cutting edges: Full-Flush

Cutting capacity: soft wire 1.3 mm (16 AWG)

Body material: Carbon Steel (C70)

Body finishing: Phosphated

Picture:



Dimensions: OAL (A) 140.0 mm – 5.512 inch
 Width 85.0 mm – 3.346 inch
 Height 13.0 mm – 0.512 inch

Head dimensions: Width (C) 13.5 mm – 0.531 inch
 Thickness (D) 5.0 mm – 0.197 inch
 B 10.0 mm – 0.394 inch
 F 2.0 mm – 0.079 inch

