

Product Datasheet

Product code: **PC2050ME**

Product type: TEK-ME Carbon Steel Hand tools

Made in: Italy

Description: The PC2050ME is an angled flush cutter. Its micro size (2mm thick) and its light and ergonomic line make it ideal for work in hard-to-access areas and for delicate work in electronics. In addition, its 50° angled head provides excellent visibility when used in either vertical or horizontal position. The cutters are equipped with an ESD and ergonomic handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharges.

Head description: Angled Micro, Shear

Cutting edges: Full-Flush

Cutting capacity: soft wire 0.64 mm (22 AWG)

Body material: Carbon Steel (C70)

Body finishing: Phosphated

Picture:



Dimensions:

OAL (A)	131.0 mm – 5.157 inch
Width	70.0 mm – 2.756 inch
Height	13.0 mm – 0.512 inch

Head dimensions:

Width (C)	10.0 mm – 0.394 inch
Thickness (D)	5.0 mm – 0.197 inch
B	8.0 mm – 0.315 inch
F	1.0 mm – 0.039 inch

