

Product Datasheet

Product code: **PC20ME**

Product type: TEK-ME Carbon Steel Hand tools

Made in: Italy

Description: The PC20ME is a flush cutter. Its micro size (2mm thick) and its light and ergonomic line make it ideal for work in hard-to-access areas and for delicate work in electronics. The cutters are equipped with an ESD and ergonomic handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharges.

Head description: Micro, Shear

Cutting edges: Full-Flush

Cutting capacity: soft wire 1.3 mm (16 AWG)

Body material: Carbon Steel (C70)

Body finishing: Phosphated

Picture:



Dimensions: OAL (A) 132.0 mm – 5.197 inch
 Width 70.0 mm – 2.756 inch
 Height 13.0 mm – 0.512 inch

Head dimensions: Width (C) 9.5 mm – 0.374 inch
 Thickness (D) 4.0 mm – 0.157 inch
 B 8.0 mm – 0.315 inch
 F 1.2 mm – 0.047 inch

