

Product Datasheet

Product code: **PC25PE**

Product type: TEK-ME Carbon Steel Hand tools

Made in: Italy

Description: The PC25PE is a flush cutter. Its small size (2,5mm thick) allow the cutting of bigger electronic components than in the micro line. The very sharp cutting edges are ideal for very delicate work in electronics, allowing access in confined areas. The cutters are equipped with an ESD and ergonomic handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharges.

Head description: Small, Shear

Cutting edges: Full-Flush

Cutting capacity: soft wire 1.02 mm (18 AWG)

Body material: Carbon Steel (C70)

Body finishing: Phosphated

Picture:



Dimensions: OAL (A) 132.0 mm – 5.197 inch
Width 75.0 mm – 2.953 inch
Height 13.0 mm – 0.512 inch

Head dimensions: Width (C) 10.0 mm – 0.394 inch
Thickness (D) 5.0 mm – 0.197 inch
B 8.0 mm – 0.315 inch
F 1.3 mm – 0.051 inch

