

## Product Datasheet

**Product code:** **PC3058E**

**Product type:** TEK-ME Carbon Steel Hand tools

**Made in:** Italy

**Description:** The PC3058E is a flush cutter. Its medium size (3mm thick) and the special treatment of the cutting edges makes this tool suitable for cutting ferrous materials. The cutters are equipped with an ESD and ergonomic handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharges.

**Head description:** Medium, Shear

**Cutting edges:** Flush

**Cutting capacity:** soft wire 1.63 mm (14 AWG)

**Body material:** Carbon Steel (C70)

**Body finishing:** Phosphated

**Picture:**



**Dimensions:** OAL (A) 138.0 mm – 5.433 inch  
 Width 85.0 mm – 3.346 inch  
 Height 15.0 mm – 0.591 inch

**Head dimensions:** Width (C) 13.5 mm – 0.531 inch  
 Thickness (D) 6.0 mm – 0.236 inch  
 B 8.0 mm – 0.315 inch  
 F 2.0 mm – 0.079 inch

