

Product Datasheet

Product code: **PC30E**

Product type: TEK-ME Carbon Steel Hand tools

Made in: Italy

Description: The PC30E is a flush cutter. Its medium size (3mm thick) allow the cutting of bigger electronic components than in the micro line. The cutters are equipped with an ESD and ergonomic handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharges. The cutter is also equipped with an anti-reflection and anti-oxidation surface treatment (phosphate coating)

Head description: Medium, Shear

Cutting edges: Full-Flush

Cutting capacity: soft wire 1.3 mm (16 AWG)

Body material: Carbon Steel (C70)

Body finishing: Phosphated

Picture:



Dimensions: OAL (A) 138.0 mm – 5.433 inch
 Width 85.0 mm – 3.346 inch
 Height 15.0 mm – 0.591 inch

Head dimensions: Width (C) 13.5 mm – 0.531 inch
 Thickness (D) 6.0 mm – 0.236 inch
 B 8.0 mm – 0.315 inch
 F 2.5 mm – 0.098 inch

