

Product information

97 49 09

- Application: insulated + non-insulated wire ferrules 10 / 16 / 25 mm²
- Approved crimping according to UL in conjunction with KNIPEX wire ferrules 97 99 330 - 399

Crimping die

For wire ferrules



General

Article No.	97 49 09
EAN	4003773030881
Weight	50 g
Dimensions	50 x 12 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details



Application	insulated and non-insulated wire ferrules
Capacity in square millimetres	10 / 16 / 25 mm ²
Number of crimp profiles	3
AWG	8 / 6 / 4

technical change and errors excepted