



"Stainless steel wall mounted industrial box, PanelSeT SBX, 200x400x120 mm, IP66"

NSYSBX204012

EAN Code: 3606481715210

Main

Range	PanelSeT	
Product name	PanelSeT SBX	
Device application	Multi-purpose	
Category	Industrial box	
Device short name	SBX	
Enclosure type	Flat face box	
Enclosure nominal height	200 mm	
Enclosure nominal width	400 mm	
Enclosure nominal depth	120 mm	
enclosure mounting	Wall mounted	
Device composition	4 cover screw 1 cover 1 body	
Body type	Single piece body folded and welded	
Type of front cover	Plain door	
Cover fixing	Half turn metal screw	
Lock type	Captive screw PZ2 outside sealed area	
Removable parts	Cover by captive screws	

Complementary

Material	Stainless steel 304L	
Surface finish	Scotch-Brite® brushed	
Standards	IEC 62208	
Product certifications	BV BVM UL	
IP degree of protection	IP66 conforming to IEC 60529	
IK degree of protection	IK10 conforming to IEC 62262	
Ambient air temperature for storage	-3560 °C	
Operating temperature	-3580 °C	
Net weight	3.2 kg	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	41.5 cm
Package 1 Width	21.5 cm
Package 1 Length	13.5 cm
Package 1 Weight	3.078 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features

