



<b>Dimensions :</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	500	400	230
inch :	19.69	15.75	9.06

#### **Materials :**

Material :	Glass Fiber Reinforced Polyester
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

#### **Temperatures :**

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

#### **Accessories :**

MF 5040	Mounting Frame with DIN-rails, for enclosures: (500 x 400 x 1)
FP 5040-3x18	Front Plate with DIN openings, for enclosures: (500 x 400 x 1)
MB CAB	Swing door kit (187 x 145 x 29)
MPP 5040	Mounting Plate, for enclosures: (500 x 400 x 2)
MP 5040	Mounting plate, for enclosures: (500 x 400 x 2)
MPX 5040	Mounting Plate, for enclosures: (500 x 400 x 1)
FP 5040-D	Swing door/Front plate, for enclosures: (500 x 400 x 1)

#### **Ratings :**

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK10;
electrical_insulation :	Totally insulated
UV resistance :	UL 746C
Flammability Rating :	UL 94 HB
Glow Wire Test (IEC 695-2-1) °C :	960C