



**Dimensions :**

	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	390	316	167
inch :	15.35	12.44	6.57

**Materials :**

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	Smoked grey
Gasket material :	Polyurethane

**Temperatures :**

Temperature °C (short term) :	-40 ... 120
Temperature °C (continuous) :	-40 ... 80
Temperature °F (short term) :	-40 ... 250
Temperature °F (continuous) :	-40 ... 175

**Accessories :**

FP 36/31	Front plate (aluminium), for enclosures: (353 x 223 x 1)
MP 36/31	Mounting plate, for enclosures: (345 x 258 x 1.5)

**Ratings :**

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK07;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

**Certificates :**

SGSFIMKO\_CARDpc