

FCE 2x64 Set



Sample image

Order symbol : FCE 2x64 Set

Product nr : 3576157

Description : Suitable for flange size 2, IP44

Remarks : Bushing points: 2 x 30mm – 64mm, 2 x 8mm – 20mm

EAN : 6418074320858

El. number :

- Finland : 3424749
- Denmark : 8212052741
- Sweden : 2600090

3576157_FIBOX_FME_2x64_DIM

Dimensions :	Height	Width	Depth
mm :	94	216	39
inch :	3.7	8.5	1.54

Materials :

Material :	TPE
Gasket material :	TPE

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

Ingress protection (EN 60529):	IP65;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 V0