

FMF 25 Set



Sample image

Order symbol : FMF 25 Set

Product nr : 3576153

Description : Suitable for flange size 2, IP55/65

Remarks : Bushing points: 1 x 20 mm - 26 mm IP65 / 12-15 mm IP55, 16 x 8 mm - 14 mm IP65 / 7 - 10 mm IP55, 4 x 14 mm - 20 mm IP65 / 5 - 10 mm IP55, 4 x 5 mm - 7 mm IP65

EAN : 6418074320810

El. number :

- Finland : 3424745
- Denmark : 8212052709
- Sweden : 2600086

3576153_FIBOX_FMF_25_DIM

Dimensions :	Height	Width	Depth
mm :	84	216	25
inch :	3.31	8.5	0.98

Materials :

Material :	TPE
Gasket material :	TPE

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

Ingress protection (EN 60529):	IP65;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 V0