

# FMF 3 Set



Sample image

**Order symbol :** FMF 3 Set

**Product nr :** 3576151

**Description :** Suitable for flange size 2, IP65

**Remarks :** Bushing points: 2 x 24 mm - 54 mm, 1 x 30 mm -59 mm, 3 x 6 mm -14 mm

**EAN :** 6418074320797

**El. number :**

- Finland : 3424743
- Denmark : 8212052686
- Sweden : 2600084

3576151\_FIBOX\_FMF\_3\_DIM

<b>Dimensions :</b>	<b>Height</b>	<b>Width</b>	<b>Depth</b>
mm :	82	214	20
inch :	3.23	8.43	0.79

**Materials :**

Material :	TPE
Gasket material :	TPE

**Temperatures :**

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

**Ratings :**

Ingress protection (EN 60529):	IP65;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 V0