

FMF 50 Set



Sample image

Order symbol : FMF 50 Set

Product nr : 3576155

Description : Suitable for flange size 2, IP65

Remarks : Bushing points: 49 x 7 mm – 13 mm1 x 15 mm – 25 mm

EAN : 6418074320834

El. number :

- Finland : 3424747
- Denmark : 8212052725
- Sweden : 2600088

3576155_FIBOX_FMF_50_DIM

Dimensions :	Height	Width	Depth
mm :	84	216	25
inch :	3.31	8.5	0.98

Materials :

Material :	TPE
Gasket material :	TPE

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

Ingress protection (EN 60529):	IP65;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 V0