

# PXP0037 Datasheet

## Product Name // IP67 Sealed HDMI Panel Mount Coupler with Sealing Cap

[View Product Page](#)


### // Product Description:

- ⊕ IP67 Sealed HDMI Panel Mount Coupler with Sealing Cap
- ⊕ Attached dust cap
- ⊕ Threaded couplings Rated to IP67
- ⊕ Gold plated Contact ensures reliable and repeated connections
- ⊕ Mates with Flex Sealed HDMI Cable Assembly PXP0036 XMXX

### // General Information:

Product Display Title:	Front Panel Mount Connector
Product Family:	Circular Data Connectors
Product Series:	30 Series HDMI
Body Colour:	Black
Body Material:	PBT+GF
Body Material Type:	Plastic Body
Contact Pin Material:	Phosphor Bronze, Gold plated
Contact Type:	Socket Contact
Coupling Type:	Screw
Data Cable Type:	HDMI 1.4 to HDMI 1.4 Connector Assembly
Diameter Over Coupling Ring Mm:	37.87mm
Dielectric Withstanding Voltage:	300V AC
Durability:	1000
Fixing Nut Material:	PBT+GF
Flamability Rating:	UL94V-0
Function:	Front Panel Mount Connector
Insulation Resistance:	10MΩ MIN
Ip Rating:	IP67
Max Operating Temperature:	60°C
Min Operating Temperature:	-10°C
Max Panel Thickness:	2mm
Number Of Contacts:	19 Contacts
Panel Cut Out:	26.1mm x 23mm
Rohs Compliant:	Yes
Thread Size:	3/4"-14 mating+mounting
Voltage Max:	5.3

#### // Product PDF Links

[30 Series Waterproof HDMI...](#)

#### // Product 3D CAD Model Links

[PXP00373D CAD Model](#)


Have a question or project enquiry  
you'd like to talk to us about?



[Click Here To Contact Us](#)