

# EMI-Ferrite Bead



## BKP250PWR-KIT JIS 2520 Size

### Designer Kit Contents

Pulse - Std Power Part Number	L (mm)	W(mm)	T (mm)	SIZE Code (JIS/EIA)	Inductance (μH)	Tolerance (±%)	RDC(Ω) Max.	Rated Current (mA)	Quantity
BKPE00252010R24MA2	2.5	2.0	1.0	2520	0.24	20	0.024	4.1	20
BKPE00252010R24TA2	2.5	2.0	1.0	2520	0.24	30	0.024	4.1	20
BKPB00252010R47MA6	2.5	2.0	1.0	2520	0.47	20	0.04	1.8	20
BKPB00252010R47MA2	2.5	2.0	1.0	2520	0.47	20	0.04	1.8	20
BKPB00252010R47TA2	2.5	2.0	1.0	2520	0.47	30	0.04	1.8	20
BKPB00252010R47TA6	2.5	2.0	1.0	2520	0.47	30	0.04	1.8	20
BKPE00252010R47MA2	2.5	2.0	1.0	2520	0.47	20	0.04	3	20
BKPE00252010R47TA2	2.5	2.0	1.0	2520	0.47	30	0.04	3	20
BKPB00252012R47MA2	2.5	2.0	1.2	2520	0.47	20	0.04	1.8	20
BKPB00252012R47TA2	2.5	2.0	1.2	2520	0.47	30	0.04	1.8	20
BKPA002520101R0M00	2.5	2.0	1.0	2520	1	20	0.11	1.2	20
BKPA002520101R0T00	2.5	2.0	1.0	2520	1	30	0.11	1.2	20
BKPB002520101R0MA2	2.5	2.0	1.0	2520	1	20	0.06	1.5	20
BKPB002520101R0MA6	2.5	2.0	1.0	2520	1	20	0.055	1.6	20
BKPB002520101R0TA2	2.5	2.0	1.0	2520	1	30	0.06	1.5	20
BKPB002520101R0TA6	2.5	2.0	1.0	2520	1	30	0.055	1.6	20
BKPE002520101R0MA2	2.5	2.0	1.0	2520	1	20	0.05	2.9	20
BKPE002520101R0TA2	2.5	2.0	1.0	2520	1	30	0.05	2.9	20
BKPB002520121R0MA2	2.5	2.0	1.2	2520	1	20	0.05	1.6	20
BKPB002520121R0TA2	2.5	2.0	1.2	2520	1	30	0.05	1.6	20
BKPB002520101R5MA2	2.5	2.0	1.0	2520	1.5	20	0.07	1.4	20
BKPB002520101R5TA2	2.5	2.0	1.0	2520	1.5	30	0.07	1.4	20
BKPB002520121R5MA2	2.5	2.0	1.2	2520	1.5	20	0.07	1.4	20
BKPB002520121R5TA2	2.5	2.0	1.2	2520	1.5	30	0.07	1.4	20
BKPA002520102R2T00	2.5	2.0	1.0	2520	2.2	30	0.15	1	20
BKPB002520102R2MA2	2.5	2.0	1.0	2520	2.2	20	0.1	1.2	20
BKPB002520102R2MA6	2.5	2.0	1.0	2520	2.2	20	0.08	1.3	20
BKPB002520102R2TA2	2.5	2.0	1.0	2520	2.2	30	0.1	1.2	20
BKPB002520102R2TA6	2.5	2.0	1.0	2520	2.2	30	0.08	1.3	20
BKPE002520102R2MA2	2.5	2.0	1.0	2520	2.2	20	0.11	1.6	20
BKPE002520102R2TA2	2.5	2.0	1.0	2520	2.2	30	0.11	1.6	20
BKPB002520122R2MA2	2.5	2.0	1.2	2520	2.2	20	0.1	1.2	20
BKPB002520122R2TA2	2.5	2.0	1.2	2520	2.2	30	0.1	1.2	20
BKPA002520103R3M00	2.5	2.0	1.0	2520	3.3	20	0.18	1	20
BKPA002520103R3T00	2.5	2.0	1.0	2520	3.3	30	0.18	1	20
BKPB002520103R3MA6	2.5	2.0	1.0	2520	3.3	20	0.1	1.2	20
BKPB002520103R3MA2	2.5	2.0	1.0	2520	3.3	20	0.12	1.1	20
BKPB002520103R3TA2	2.5	2.0	1.0	2520	3.3	30	0.12	1.1	20
BKPB002520103R3TA6	2.5	2.0	1.0	2520	3.3	30	0.1	1.2	20
BKPB002520123R3MA2	2.5	2.0	1.2	2520	3.3	20	0.12	1.1	20
BKPB002520123R3TA2	2.5	2.0	1.2	2520	3.3	30	0.12	1.1	20
BKPA002520104R7M00	2.5	2.0	1.0	2520	4.7	20	0.25	0.9	20
BKPA002520104R7T00	2.5	2.0	1.0	2520	4.7	30	0.25	0.9	20
BKPB002520104R7MA6	2.5	2.0	1.0	2520	4.7	20	0.11	1.1	20
BKPB002520104R7MA2	2.5	2.0	1.0	2520	4.7	20	0.14	1	20
BKPB002520104R7TA2	2.5	2.0	1.0	2520	4.7	30	0.14	1	20
BKPB002520104R7TA6	2.5	2.0	1.0	2520	4.7	30	0.11	1.1	20
BKPB002520124R7MA2	2.5	2.0	1.2	2520	4.7	20	0.14	1	20
BKPB002520124R7TA2	2.5	2.0	1.2	2520	4.7	30	0.14	1	20

# EMI-Ferrite Bead



## BKP250PWR-KIT JIS 2520 Size

---

### Dimensions – Millimeters (Inches)

